


Sandwich plate H10-1662, mounting interface acc. DIN 24340-A10, CETOP 05 / NG10 for A-regeneration



p/Q performance curves




Measured with valves D31FP/FB/FC*, spool Z31 at command signal 100 %.

Curves for D3W, D31NW, D3FB and D3FP on request.


Dimensions



Symbol	Ordering code	 Kit		Torque	 Kit
	H10-1662 CETOP 05 (O-rings included in delivery)	BK412	4x M6x90 ISO 4762-12.9	13.2 Nm ±15 %	NBR: SK-H10-1662

Sandwich plate H10-1666L, mounting interface acc. DIN 24340-A10, CETOP 05 / NG10 for hybrid function



p/Q performance curves




Measured with valves D31FP/FE/FB/FC*, spool Z31 at command signal 100 %.

Curves for D3W, D31NW, D3FB and D3FP on request.

Dimensions



Symbol	Ordering code	 Kit		Torque	 Kit
	H10-1666L CETOP 05 (O-rings included in delivery)	BK528	4x M6x110 ISO 4762-12.9	13.2 Nm ±15 %	NBR: SK-H10-1666